



Thermobonded pleated filter bag with increased dirt-holding capacity

Eaton's MAX-LOAD extended life thermobonded pleated filter bags offer solutions to a wide range of applications requiring dramatically increased capacity applicable in all industrial processes.

MAX-LOAD pleated filter bags are manufactured from nominal rated extended-life needle felt filter media. The pleated media construction combined with the filter media results in up to 10 times increased dirt-holding capacity compared to similar sized standard needle felt.

Features and benefits

- Pleated media structure allows for 4 times more surface area compared to a similar size standard filter bags in the same bag housing
- Available in polypropylene with matching end caps and seal rings to cover most processing conditions
- Thermo-bonded end caps provide a strong, bypass-free and seamless construction
- Extended-life needle felt filter media can cover a wide range of filtration needs

- Fits in all Eaton standard size 01 and 02 restrainer baskets
- Produced according to Eaton's silicon-free process¹
- Patented SENTINEL® seal ring provides 100% bypass-free filtration
- Outer cage structure provides additional support against harsh conditions

Filter specifications

Materials
Needle felt (POXL):
Polypropylene

Seal rings
SENTINEL seal ring with end caps in polypropylene and polyester copolymer

Retention ratings
1, 5, 10, 25 and 50 µm nominal

Dimensions/Parameters

Sizes

01: Ø 180 x 345 mm L
02: Ø 180 x 730 mm L

Filter area

01: 0.8 m²
02: 1.6 m²

Max. operating temperature

Polypropylene: 90 °C

Max. differential pressure

2.5 bar

Recommended change-out pressure for disposal²

0.8 – 1.5 bar

Max. flow rates³

01: 10 m³/h
02: 20 m³/h

MAX-LOAD Pleated Filter Bag Range



Strong cage supports the filter element during harsh conditions




Pleated structure with extended-life media provides vastly increased dirt-holding capacity



Bypass-free sealing through SENTINEL seal ring

Ordering information



¹ Based on an accepted paint compatibility test (see document QUC-STA-10).

² Depending on the respective application requirements.

³ For liquids with a dynamic viscosity of 1 mPa·s @ 20 °C.

For more information:

WEB: FLTR.com.au PHONE: (+61) 1300 62 4020 EMAIL: info@FLTR.com.au SKYPE: Purple.Engineering